



Since the wall mountingset has two stages, the distances from the wall are indicated in the table below according to the two stages

Product Name	Tube	Height (mm)	Width (mm)	Pipework Center (mm)	Thickness (mm)	Wall to Back (mm)	Wall to Pipe Center (mm)	Wall to Front (mm)
Hamilton Double	7	580	404	545	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	10	580	581	545	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	14	580	817	545	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	17	580	994	545	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	20	580	1171	545	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	24	580	1407	545	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	5	1780	286	1745	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	6	1780	345	1745	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	7	1780	404	1745	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	8	1780	463	1745	74,5	26/35	63,25/72,25	100,50/109,50
Hamilton Double	9	1780	522	1745	74,5	26/35	63,25/72,25	100,50/109,50